



Operating Temperature: 75°C max.

Material : Copper
 Terminal : PVC
 Insulation : TIN

Best.-Nr.	WIRE RANGE mm ² / AWG	DIMENSION						COLOR
		TAB (mm)	W (mm)	B (mm)	Dø (mm)	dø (mm)	L (mm)	
74 50 60	0.5~1.5mm ² 22~16 AWG	0.8×6.35	9.3	6.5	3.8	1.7	23	RED
74 50 73	1.5~2.5mm ² 16~14 AWG	0.8×6.35	9.3	6.5	6	2.6	23	BLUE
74 50 86	4~6mm ² 12~10 AWG	0.8×6.35	9.3	6.5	7	3.6	25	YELLOW

Electric rating:
 600V max
 Current: 19A max
 Current: 27A max
 Current: 48A max

Fully Insulated Female
 Dis connector Series