



Operating Temperature: 75°C max.

Material : Copper
 Terminal : PVC
 Insulation : TIN

Best.-Nr.	WIRE RANGE mm ² /AWG	DIMENSION							COLOR
		STUD SIZE	d2 (mm)	B (mm)	L (mm)	F (mm)	H (mm)	Dø (mm)	
74 52 24	0.5~1.5mm ² 22~16 AWG	M3 (3.2mm)	3.2	5.7	21.2	6.5	10	4.3	RED
74 52 40		M3.5(3.7mm)	3.7	5.7	21.2	6.5			
74 52 54		M4 (4.3mm)	4.3	6.4	21.2	6.5			
74 52 68		M5(5.3mm)	5.3	8.1	21.2	6.5			
74 52 83		M6(6.5mm)	6.5	9.5	21.2	6.5			
74 52 98	1.5~2.5mm ² 16~14 AWG	M3(3.2mm)	3.2	5.7	21.2	6.5	10	4.9	BLUE
74 53 12		M3.5(3.7mm)	3.7	5.7	21.2	6.5			
74 53 25		M5(5.3mm)	5.3	8.1	21.2	6.5			
74 53 38		M6(6.5mm)	6.5	9.5	21.2	6.5			
74 53 52	4~6mm ² 12~10 AWG	M3(3.2mm)	3.7	8.3	25.2	7.5	13.5	6.7	YELLOW
74 53 67		M3.5(3.7mm)	4.3	8.3	25.2	7.5			
74 53 82		M5(5.3mm)	5.3	9	26	7.5			
74 53 96		M6(6.5mm)	6.5	9	26.5	7.5			

Spade Connector Series