

Single relay - REL-OR- 24DC/3X21 - 2834274

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Pluggable octal relay with power contacts, 3 PDT, test button, mechanical switching position indication, coil voltage 24 V DC

Product Features

- Extremely rugged design
- With detectable manual operation
- Mechanical switch position indicator

Key commercial data

package_quantity	10
GTIN	4017918941772

Technical data

Dimensions

Width	34.5 mm
Height	34.5 mm
Depth	52.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 60 °C

Coil side

Nominal input voltage U_N	24 V DC
Nominal input current at U_N	56 mA
Typical response time	12 ms
Typical release time	6 ms
Coil resistance	430 Ω +/-15% (at 20 °C)

Contact side

Contact type	Single contact, three PDTs
Contact material	AgSnIn
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	1 V
Maximum inrush current	(on request)
Min. switching current	10 mA

Single relay - REL-OR- 24DC/3X21 - 2834274

Technical data

Contact side

Limiting continuous current	10 A (N/O contact)
Limiting continuous current	5 A (N/C contact)
Interrupting rating (ohmic load) max.	2500 VA (for 250 V AC)

General

Test voltage relay winding/relay contact	2.5 kV AC (50 Hz, 1 min.)
Test voltage relay contact/relay contact	2.5 kV AC (50 Hz, 1 min.)
Operating mode	100% operating factor
Mechanical service life	10 x 10 ⁶ cycles
Standards/regulations	IEC 60664
Pollution degree	3
Surge voltage category	II
Mounting position	Any
Assembly instructions	On relay base PR3

Connection data

Connection method	Plug connection
-------------------	-----------------

classifications

eCl@ss

eCl@ss 4.0	27371104
eCl@ss 4.1	27371104
eCl@ss 5.0	27371001
eCl@ss 5.1	27371001
eCl@ss 6.0	27371001
eCl@ss 7.0	27371001
eCl@ss 8.0	27371001

ETIM

ETIM 2.0	EC000196
ETIM 3.0	EC000196
ETIM 4.0	EC000196
ETIM 5.0	EC000196

UNSPSC



UNSPSC 6.01	30211916
UNSPSC 7.0901	39121515
UNSPSC 11	39121515
UNSPSC 12.01	39121515
UNSPSC 13.2	39121515

Single relay - REL-OR- 24DC/3X21 - 2834274

approvals

UL Recognized / cUL Recognized / cULus Recognized /


Approval details



Drawings

Single relay - REL-OR- 24DC/3X21 - 2834274


Diagram



Interrupting rating

Single relay - REL-OR- 24DC/3X21 - 2834274


Diagram



Electrical service life

Single relay - REL-OR- 24DC/3X21 - 2834274

Diagram



Service life reduction factor with various cos phi

Circuit diagram

