



Best.-Nr.	WIRE RANGE mm ² / AWG	DIMENSION							COLOR
		STUD SIZE	d2ø (mm)	B (mm)	L (mm)	F (mm)	H (mm)	Dø (mm)	
74 55 01	0.5~1.5mm ² 22~16 AWG	M3 (3.2mm)	3.2	5.7	17.8	4.95	10	4.2	RED
74 60 36		M3.5(3.7mm)	3.7	5.7	18.1	6.3			
74 60 48		M4 (4.3mm)	4.2	6.6	20.1	5.7			
74 60 61		M5(5.3mm)	5.2	8	21.5	6.7			
74 60 74		M6(6.5mm)	6.4	11.6	27.5	10.5			
74 67 62		M8(8.4mm)	8.4	11.6	27.5	11.1			
74 60 87	1.5~2.5mm ² 16~14 AWG	M3 (3.2mm)	3.2	6.6	18.6	4.3	10	4.7	BLUE
74 64 27		M3.5(3.7mm)	3.7	6.6	17.8	4.3			
74 65 42		M4 (4.3mm)	4.2	6.6	21	6.4			
74 65 55		M5(5.3mm)	5.2	8.5	22.5	7			
74 65 68		M6(6.5mm)	6.4	12	27.6	10.5			
74 65 81		M8(8.4mm)	8.4	12	27.6	11			
74 65 94	4~6mm ² 12~10 AWG	M3.5(3.7mm)	3.7	7.2	22.7	5.9	13.5	6	YELLOW
74 66 28		M4 (4.3mm)	4.3	7.2	22.8	5.9			
74 66 21		M5(5.3mm)	5.3	9.5	26.3	7.7			
74 66 82		M6(6.5mm)	6.4	12	29	9.2			
74 67 50		M8(8.4mm)	8.4	15	34.5	13.7			

Ring Connector Series