

**Industrial Ethernet
IE-FCM-RJ45-FJ-P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Service interface FrontCom[®] Micro with RJ45 in IP65**General ordering data**

Type	IE-FCM-RJ45-FJ-P
Order No.	1018830000
Version	FrontCom Micro RJ45 module, PROFINET
GTIN (EAN)	4032248730087
Qty.	10 pc(s).

Industrial Ethernet IE-FCM-RJ45-FJ-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Wall thickness, max.	3 mm	Wall thickness, min.	1 mm
Net weight	33.7 g		

Temperatures

Operating temperature	-40 °C...+70 °C	Storage temperature	
Installation temperature			

Downloads

Installation video	STEADYTEC® assembly instruction RJ45 field attachable module_EN_HD.mp4	UL Approval	DUXR.E316369.pdf
--------------------	--	-------------	------------------

General data

Category	Cat.5 (ISO/IEC 11801)	Colour	Black
Connection 1	RJ45	Connection 2	IDC
Contact surface	Gold over nickel	Description of article	FrontCom Micro RJ45 module
Housing main material	PA UL 94 V0	Insulation cross-section, max.	1.6 mm
Plugging cycles	750	Protection degree	IP 65 according to DIN EN 60529
Sheath diameter, max.	10 mm	Sheath diameter, min.	5.5 mm
Shielding	360° shield contact	Type of mounting	Cabinet, Distribution box
Wire connection diameter, flexible, max.	0.76 mm	Wire connection diameter, flexible, min.	0.48 mm
Wire connection diameter, solid, max.	0.64 mm	Wire connection diameter, solid, min.	0.4 mm
Wire cross-section, finely stranded, max. (AWG)	AWG 22	Wire cross-section, finely stranded, min. (AWG)	AWG 26
Wiring	PROFINET		

Electrical properties

PoE PoE+	conforming to IEEE 802.3af
----------	----------------------------

Standards

Connector standard	IEC 60603-7-51
--------------------	----------------

Classifications

ETIM 3.0	EC001134	eClass 5.1	27-25-05-04
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04

Approvals

Approvals




ROHS	Conform
------	---------

Industrial Ethernet IE-FCM-RJ45-FJ-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Dimensioned drawing



Installation cut-out

