


No.	Changes and/or Note No.	Date	Intr.	No.	Changes and/or Note No.	Date	Intr.



Dimensions:

SIZE	A	B	C	F (Footprint)
9	16,30	24,99	30,81	7,2 / 9,4
15	24,60	33,32	39,14	7,2 / 9,4
25	38,30	47,04	53,04	7,2 / 9,4
37	54,80	63,50	69,32	7,2 / 9,4

How to order:

SIZE	7,2mm	9,4mm
9	2103-1100-11	2103-2100-11
15	2103-1100-12	2103-2100-12
25	2103-1100-13	2103-2100-13
37	2103-1100-14	2103-2100-14

Technical & Mechanical Specifications:

Shell: Steel, Tin Plated
 Insulator: Black, PBT - UL94 V-0
 Contacts: Copper Alloy
 Contact Plating: Gold Flash
 Mounting Accessories: "Z" Snap Lock + Hex-screw
 Other Mounting types on request

Current Rating: 5 Amp Max.
 Contact Resistance: 10mΩ Max.
 Operating Temperature: -55°C to +105°C
 Withstanding Voltage: 1000V AC for 1 minute
 Insulator Resistance: 1000MΩ min,

DATE 2012-05-24	DRAWN MRR	SCALE	MATERIAL TYPE
	APPROVED		REPLACES
DRA-xxFTBG-110 - 7,2mm DRB-xxFTBG-110 - 9,4mm			DRAWING No