



ITEM-NO. (ITEM-NO.)	255-402/000-009/999-950
Cross section1 (Cross section / mm²)	0.5 - 2.5
Cross section2 (Cross section / AWG)	20 - 12
Strip length (Strip length / mm)	5 - 6
Measured voltage (Measured voltage / V)	275
Measured shock voltage (Measured shock voltage / kV)	
Pollution degree (Pollution degree)	
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	2
Height (Height / mm)	14.2
Width (Width / mm)	12.9
Depth (Depth / mm)	18.3
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	2
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	2.548
Comment (Comment)	L = (No. of poles x Pin Spacing) + 2,9 mm
Dimensions (Dimensions)	1,1 + 0,1 mm