



**MODULAR PCB TERMINAL BLOCK 2
SOLDER PINS / POLE 1 POLE PIN
SPACING 10/10.16 MM / 0.4 IN WITH
PUSH BOTTONS
255-601**

ITEM-NO. (ITEM-NO.)	255-760
Cross section1 (Cross section / mm²)	0,08 - 2,5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	5 - 6
Measured voltage (Measured voltage / V)	1000
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	24
RM (PIN SPACING / mm)	10
P (NO. OF POLES)	1
Height (Height / mm)	14.2
Width (Width / mm)	10
Depth (Depth / mm)	18.3
No. of connection Points (No. of connection Points)	1
No. of potentials (No. of potentials)	1
COLOR (COLOR)	rot
WEIGHT (WEIGHT / g)	
Dimensions (Dimensions)	1,1 + 0,1 mm