

Connector - SACC-M 8FS-3CON-M - 1681172

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator connector, female, straight, 3-pos., M8, solder connection, metal knurl, cable diameter max. 5 mm

Product Features

- ✓ Safe use in the field, thanks to a high degree of protection
- ✓ Flexible: connectors for on-site assembly

Key commercial data

package_quantity	1
GTIN	4017918157524

Technical data

Dimensions

External diameter	3.5 mm ... 5 mm
Stripping length of the sheath	12 mm
Stripping length of the individual wire	3 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Degree of protection	IP67

General

Rated current at 40 °C	4 A
Rated voltage	60 V
Number of positions	3
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M8 connector IEC 61076-2-104
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Solder connection
Conductor cross section	0.08 mm² ... 0.25 mm²
AWG conductor cross section	28 ... 22

Connector - SACC-M 8FS-3CON-M - 1681172

Technical data

General

Insertion/withdrawal cycles	≥ 100
Torque	0.2 Nm (M8 knurl)

Material

Inflammability class according to UL 94	V0
Contact material	CuSn
Contact surface material	Au
Contact carrier material	PUR / PA66
Material of grip body	PBT
Material, knurls	Nickel-plated brass
Sealing material	NBR

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27279221
eCl@ss 7.0	27440104
eCl@ss 8.0	27440104

ETIM

ETIM 2.0	EC001121
ETIM 3.0	EC002062
ETIM 4.0	EC002062
ETIM 5.0	EC002062

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

GOST / GOST /

Approval details

Connector - SACC-M 8FS-3CON-M - 1681172

approvals



accessories

Seal

SACC-M 8-SET/2,2-3,5 - 1436945



Torque tool

TSD 02 SAC - 1208487



TSD-M 1,2NM - 1212224



Screwdriver tools

SACC BIT M8-D12 - 1208474



Connector - SACC-M 8FS-3CON-M - 1681172

accessories

TSD-M SAC-BIT ADAPTER - 1212600



Protective cap

PROT-M 8 MS-PA-CHAIN - 1430860



Cable by the meter


SAC-3P-100,0-PUR/0,25 - 1501689



Drawings

Connector - SACC-M 8FS-3CON-M - 1681172


Dimensioned drawing



Socket M8 x 1, straight

Connector - SACC-M 8FS-3CON-M - 1681172


Schematic diagram



Pin assignment M8 socket, 3-pos.

Connector - SACC-M 8FS-3CON-M - 1681172

Schematic diagram



1 = pressure screw 2 = clamp-type cage 3 = gasket 4 = housing 5 = male or female insert

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>