

Zack marker strip - ZB 6,LGS:(1-100/VERP.) - 1051919

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Zack marker strip, Strip, white, labeled, Printed horizontally: Consecutive numbers, Mounting type: Snap into tall marker groove, For terminal block width: 6.2 mm, Lettering field: 10.5 x 6.15 mm

The illustration shows the version
ZB 6:UNBEDRUCKT

Key commercial data

package_quantity	1
GTIN	4017918255725

Technical data

Dimensions

Width (a)	6 mm
-----------	------

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C

General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Printing direction	Printed horizontally
Printing	Consecutive numbers
Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10

classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137

Zack marker strip - ZB 6,LGS:(1-100/VERP.) - 1051919

classifications

eCl@ss

eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Drawings