



749237

DC power cable

- 1) Cable length: 2M
- 2) Plug style: straight
- 3) Plated Tim: 6 mm (Length)
- 4) double cable: 2x0.4mm²
- 5) Out dia.: 5.5mm, inner dia. 2.5mm.
- 6) Color: Red/Black
- 7) max. operating voltage and current: 36V 5A
- 8) - Red cable: outer dia: 2.5mm and inner dia: 0.8mm
 - Black cable: outer dia: 2.5mm and inner dia: 0.8mm

F/N: 93025c181
Old B/N: 738477
New B/N: 749237
M/N: DC-2G25-XL