

Han Hand Crimp Tool



Image is for illustration purposes only. Please refer to product description.

Part number	09 99 000 0110
Specification	Han Hand Crimp Tool
HARTING eCatalogue	https://b2b.harting.com/09990000110

Identification

Category	Tools
Type of tool	Hand crimping tool
Description of the tool	Han D [®] : 0.14 ... 1.5 mm ² (in the range from 0.14 ... 0.37 mm ² only suitable for contacts 09 15 000 6104/6204 and 09 15 000 6124/6224) Han E [®] : 0.5 ... 4 mm ² Han-Yellock [®] : 0.5 ... 4 mm ² Han [®] C: 1.5 ... 4 mm ²
Type of drive	Can be processed manually

Version

Die set	HARTING W Crimp
Direction of movement	Parallel
Field of application	Recommended for production lines up to 1,000 crimping operations per year
Pack contents	Locator Han [®] C Locator Han E [®] Locator Han D [®] Please order Han-Yellock [®] separately.

Technical characteristics

Conductor cross-section	0.14 ... 4 mm ²
Cycles cleaning / inspection	100
Cycles crimp check	1,000
Cycles service / maintenance	10.000 (at least once a year)



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	680 g
Country of origin	Germany
European customs tariff number	82032000
GTIN	5713140105577
ETIM	EC000168
eCl@ss	21043811 Crimping pliers