


DO NOT SCALE
DIMENSIONS IN mm



METRIC

THIRD ANGLE
PROJECTION




NOTES:


- ① CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1,27 CENTERS .
FOR CABLE REQUIREMENTS SEE AMP APPLICATION SPECIFICATION 114-19022.
- ② THESE RECEPTACLE CONNECTORS MATE WITH 0,64 ^{10,05} mm SQUARE OR ROUND POSTS
ON 2,54mm GRID.
- ③ MARK INDICATING FIRST CABLE POSITION REFERRING TO CONTACT POSITION.
- ④ THERE IS NO POLARIZATION-SLOT AT THIS END IN 6, 10 AND 14 POS CONNECTORS.
- ⑤ THESE CONNECTORS CAN BE USED IN CONJUNCTION WITH STRAIN-RELIEF COVERS
OF PARTNR: 100103.
- ⑥ THERE IS NO POLARIZATION-SLOT AT THIS END IN 6 POS CONNECTORS.
- ⑦ PRODUCT SPECIFICATION 108-19033.



CONNECTOR HEIGHT
AFTER CABLE
TERMINATION. ①



85,9	64	32	6-215882-4	E
80,8	60	30	6-215882-0	E
68,1	50	25	6-215882-0	E
60,5	44	22	4-215882-4	E
55,4	40	20	4-215882-0	E
47,8	34	17	3-215882-4	E
42,7	30	15	3-215882-0	E
37,6	26	13	2-215882-6	E
30,0	20	10	2-215882-0	E
24,9	16	8	1-215882-6	E
22,4	14	7	1-215882-4	E
17,3	10	5	1-215882-0	E
OBSOLETE	14,8	8	4-0-215882-8	C
OBSOLETE	12,2	6	3-0-215882-6	E
OBSOLETE	9,7	4	2-0-215882-4	C
DIM. "C"	"B" CABLE POS.	"A" DUAL POS.	PARTNUMBER	PART REV.



③ RECEPTACLE CONTACT	PHOSPHORBRONZE Cu Sn6	AT CONTACT-PLACE: 0,8µm GOLD AT WIRING END: 2,5µm TIN ENTIRE UNDERCOATING: 1,27µm NICKEL
② COVER	THERMOPLASTIC POLYESTER GF UL 94 -V0	GREY RAL 7032 (ONLY FOR REF.)
① HOUSING		
COMPONENT NAME	MATERIAL	PLATING / COLOUR

CUSTOMER DRAWING				FOR REFERENCE ONLY. WILL NOT BE UPDATED			
E5	ECR06-29576	A.V.	R.M.	15-12-06	 AMP ITALIA S.p.A Corso F.LLI Cervi, 15 COLLEGNO (TORINO)		
E4	ET00-0243-04	A.V.	R.M.	21-03-05			
E3	ET00-0159-04	A.V.	R.M.	13-07-04			
E2	ET00-0180-03	A.V.	R.M.	19-01-04			
E1	ET00-0093-03	SS	-	23-05-03			
E	H-9454	JvdH	R.V.	10-01-92	NAME AMP-LATCH_MIL-TYPE RECEPTACLE_CONNECTOR ASSEMBLY_(SYMMETRIC_COVER)		
LTR:	REVISION RECORD	DR:	CHK.	DATE			
DR.:	W.R.VERBEET	CHK.:	R.VERSTIJNEN	APP.:	LY.SOEEST	DWG.No.	SIZE
DATE:	02-02-88	DATE:	03-02-88	DATE:	03-02-88	C-215882	A3
							SHEET 1 OF 1
							REV.LTR. E5

8 7 6 5 4 3 2 1