

## SPECIFICATIONS SHEET

PRODUCT TYPE : **MAGNETIC BUZZER**

DESCRIPTION : **MT BUZZER SINGLE 12VDC L/W ABS SP RoHS**

COLOR : **BLACK**

### ELECTRICAL SPECIFICATIONS

OPERATING VOLTAGE RANGE	( VDC )	9.0 ~ 15.0
RATED VOLTAGE	( VDC )	12.0
* MAX. RATED CURRENT	( mA )	40.0
* MIN. SOUND OUTPUT	( dBA/ 30 cm )	95.0
* FREQUENCY	( Hz )	2800 ± 200
tone NATURE		SINGLE
OPERATING TEMPERATURE	( ° C )	- 20 ~ + 60
TERMINAL		LEADWIRE ( UL1007 , AWG#28 )
HOUSING MATERIAL		ABS
WEIGHT	( g )	10.0

\* Value applying at rated voltage

### DIMENSIONS

UNIT : mm

TOP VIEW

SIDE VIEW

