

Data sheet for your B/N 751041
-- CEILING MOTION ALARM w/ REMOTE CONTROL
=====

a) Supply voltage :
=====

Main Alarm unit -- battery : 4 x LR14
(Alkaline battery)
[batteries are not
included.]

Or, connected by external AC/DC Adaptor (DC 9V, 200 mA)

Infrared Remote Control -- 12VDC (1x battery type 23A)
[battery is
included]

b) Battery size :
=====

Main alarm unit -- 4 x LR 14 (Alkaline battery)
Remote control unit -- one 23A (Alkaline battery)

c) Battery liftttime :
=====

Main Alarm unit -- about 6 months (in stand-by mode)

d) Current consumption :
=====

Stand-by mode -- 1.5 mA
Alarm mode -- 100 to 120 mA

e) Alarm output :
=====

108 - 110 dB. (measured at 1 ft. from sound source)

f) Detection range :
=====

360 degree x 6 m. diameter
(installation height 2.0 - 2 .5 m from the ground.)