

# KERN 283-252

Klein, praktisch, mobil - mechanische Präzision im Westentaschenformat

**KERN**<sup>®</sup>



## Measuring system

|                        |         |
|------------------------|---------|
| Measuring range [Max]: | 3 N     |
| Precision (of [Max]):  | 0,003   |
| Readout [d]:           | 0,020 N |

## Service

|  |          |
|--|----------|
| ISO Calibration certificate (Tensile): | 961-1610 |
|--|----------|

## Category

|                |                        |
|----------------|------------------------|
| Brand:         | KERN                   |
| Category:      | Force gauges           |
| Product Group: | Mechanical force gauge |

## Packaging & shipping

|                               |                  |
|-------------------------------|------------------|
| Delivery:                     | 24 h             |
| Dimensions packaging (WxDxH): | 230 x 26 x 17 mm |
| Gross weight:                 | 47 g             |
| Net weight:                   | 32 g             |
| Shipping method:              | Parcel service   |

## Construction

|                             |                  |
|-----------------------------|------------------|
| Casing material:            | aluminium        |
| Dimensions housing (WxDxH): | 220 x 12 x 12 mm |