

# KERN 283-402

Klein, praktisch, mobil - mechanische Präzision im Westentaschenformat



## Measuring system

Measuring range [Max]:	10 N
Precision (of [Max]):	0,003
Readout [d]:	0,100 N

## Service

ISO Calibration certificate (Tensile):	961-1610
--	----------

## Category

Brand:	KERN
Category:	Force gauges
Product Group:	Mechanical force gauge

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	230 x 26 x 17 mm
Gross weight:	50 g
Net weight:	32 g
Shipping method:	Parcel service

## Construction

Casing material:	aluminium
Dimensions housing (WxDxH):	220 x 12 x 12 mm