

KERN 283-422

Klein, praktisch, mobil - mechanische Präzision im Westentaschenformat

KERN[®]



Measuring system

Measuring range [Max]:	25 N
Precision (of [Max]):	0,003
Readout [d]:	0,200 N

Service

ISO Calibration certificate (Tensile):	961-1610
--	----------

Category

Brand:	KERN
Category:	Force gauges
Product Group:	Mechanical force gauge

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	230 x 26 x 17 mm
Gross weight:	47 g
Net weight:	32 g
Shipping method:	Parcel service

Construction

Casing material:	aluminium
Dimensions housing (WxDxH):	220 x 12 x 12 mm