

# KERN 326-13

Individual weight, OIML Class F1, 5 kg, Eco Shape, stainless steel polished



|                              |                |
|------------------------------|----------------|
| Dimensions packaging (W×D×H) | 80×80×144 mm   |
| Shipping method              | Parcel service |
| Net weight approx.           | 5,0 kg         |
| Gross weight approx.         | 5,0 kg         |
| Shipping weight              | 5 kg           |

## Optional cases

|                                 |             |
|---------------------------------|-------------|
| Case - Plastic article number   | 347-130-400 |
| Case - Aluminium article number | 317-130-600 |
| Case - Wood article number      | 317-130-100 |

## Product information

|                      |                          |
|----------------------|--------------------------|
| GTIN/EAN number      | 4045761223639            |
| REACH classification | no prohibited substances |

## Pictograms

### STANDARD



### OPTION



## Category

|                  |                   |
|------------------|-------------------|
| Brand            | KERN              |
| Product category | Individual weight |
| Product group    | OIML F1           |
| Product family   | 326               |

## Measuring System

|  |       |
|--|-------|
| Test weight - Density uncertainty (kg/m <sup>3</sup> ) | 140   |
| Weight OIML class                                      | F1    |
| Test weight - nominal value                            | 5 kg  |
| Permissible tolerance according to OIML (+/-)          | 25 mg |
| Test weight - Density (kg/m <sup>3</sup> )             | 7950  |
| OIML-compliant   | ✓     |
| Test weight - Density [Min] (OIML)                     | 7390  |
| Test weight - Density [Max] (OIML)                     | 8730  |

## Construction

|                   |                          |
|-------------------|--------------------------|
| Shape weight      | Eco Shape                |
| Dimensions (Ø×H)  | 80×144 mm                |
| Material          | stainless steel polished |
| Adjustment method | Adjusting cavity - Seal  |

## Services (optional)

|  |         |
|--|---------|
| Article number for DAkks calibration         | 962-443 |
| Article number for guaranteed plus-deviation | 921-443 |

## Packing & Shipping

|               |     |
|---------------|-----|
| Delivery time | 1 d |
|---------------|-----|