

KERN 337-06

Individual weight, OIML Class F2, 50 g, Knob, stainless steel fine turned



Article number for guaranteed plus-deviation 921-436

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	18×18×29 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg

Optional cases

Case - Plastic article number	347-070-400
Case - Aluminium article number	317-060-600
Case - Wood article number	337-060-200

Product information

GTIN/EAN number	404576 1006386
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F2
Product family	337

Measuring System

Test weight - volume (cm ³)	6,25
Conformity assessment possible	no
Test weight - Density uncertainty (kg/m ³)	140
Test weight - volume uncertainty (cm ³)	0,0781
Weight OIML class	F2
Test weight - nominal value	50 g
Permissible tolerance according to OIML (+/-)	1 mg
Test weight - Density (kg/m ³)	7950
OIML-compliant	✓
Test weight - Density [Min] (OIML)	6000
Test weight - Density [Max] (OIML)	12000

Construction

Shape weight	Knob
Dimensions (Ø×H)	18×29,5 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-436
--------------------------------------	---------