

# KERN 347-07

Individual weight, OIML Class M1, 100 g, Knob, stainless steel fine turned



## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	22×22×39 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg

## Optional cases

Case - Plastic article number	347-070-400
Case - Aluminium article number	317-070-600
Case - Wood article number	337-070-200

## Product information

GTIN/EAN number	4045761008724
REACH classification	no prohibited substances

## Pictograms

### STANDARD



### OPTION



## Category

Brand	KERN
Product category	Individual weight
Product group	OIML M1
Product family	347

## Measuring System

Test weight - volume (cm <sup>3</sup> )	12,5
Conformity assessment possible	✓
Test weight - Density uncertainty (kg/m <sup>3</sup> )	140
Test weight - volume uncertainty (cm <sup>3</sup> )	0,1563
Weight OIML class	M1
Test weight - nominal value	100 g
Permissible tolerance according to OIML (+/-)	5 mg
Test weight - Density (kg/m <sup>3</sup> )	7950
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2600

## Construction

Shape weight	Knob
Dimensions (Ø×H)	22×39 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

## Services (optional)

Article number for DAkks calibration	962-637
--------------------------------------	---------