

KERN 440-47N

Der Klassiker im Labor



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US
Operating time:	12 h
Operating time (Backlight off):	20 h
Rechargeable battery:	Rchrg. battery optional

Service

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	348 x 212 x 178 mm
Gross weight:	1,564 kg
Net weight:	1,100 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	165 x 230 x 74 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	130 x 130 mm

Measuring system

Adjustment options:	External calibration
Linearity:	200 mg
n/a:	200 g
Readout [d]:	100 mg
Recommended adjusting weight:	2 kg (M1)
Reproducibility:	100 mg
Resolution:	20000
Stabilisation time:	3 s
Warm up time:	30 min
Weighing range [Max]:	2 kg
Weighing system:	Strain gauge
Weighing units:	dwt g kg lb mo oz ozt tl (HK) tl (Tw) tol

Display

Display digit height:	1,500 cm
-----------------------	----------

Counting

Counting resolution:	10000
Minimum piece weight at piece counting (Laboratory):	200 mg
Minimum piece weight at piece counting (Normal):	2 g

Functions

Counting function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes