

KERN AC 02

KERN

Ball-shaped head made of nickel-plated-steel for compression and fracture tests

Pictograms

STANDARD



Category

Brand	Sauter
Product category	Clamp
Product group	Ball-shaped head

Construction

Dimension housing (W×D×H)	35×10×10 mm
Dimensions completely mounted (W×D×H)	35×10×10 mm
Material	metal
Material housing	metal
Mounting - force dissipation	Threaded hole M10 Threaded hole M6
Tensile/compressive force [Max]	5 kN

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	150×100×10 mm
Net weight	0,04 kg
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg