

# KERN CPB 15K2DM

Profimodell auch mit Eichzulassung [M], Zählauflösung bis zu 60.000 Punkte



## Measuring system

Adjustment options:	External calibration
Linearity:	4 g   10 g
Readout [d]:	2 g   5 g
Recommended adjusting weight:	15 kg (F2)
Reproducibility:	2 g   5 g
Resolution:	3 3.000
Stabilisation time:	2 s
Tare range:	14,995 kg
Warm up time:	10 min   10 min
Weighing range [Max]:	6 kg   15 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height:	2 cm
-----------------------	------

## Technical data about verification

Minimum load [Min]:	40 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	2 g   5 g

## Counting

Counting resolution:	60000
Minimum piece weight at piece counting (Laboratory):	250 mg
Minimum piece weight at piece counting (Normal):	2,500 g
Reference weight:	yes

## Functions

Counting function:	yes
Function to save totals:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

## Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK US

n/a:

Mains adapter external

## Power supply

Operating time (Backlight off):	90 h
Operating time (Backlight on):	50 h
Rechargeable battery:	Rchrg. battery optional - intern

## Service

Adjustment at the location of installation:	961-248
DAkkS Certificate:	963-128
Verification:	965-228

## Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	450 x 375 x 220 mm
Gross weight:	4,494 kg
Net weight:	3,432 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	315 x 350 x 100 mm
Dimensions of display device (WxDxH):	315 x 350 x 125 mm

# KERN CPB 15K2DM



Profimodell auch mit Eichzulassung [M], Zählauflösung bis zu 60.000 Punkte

Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	320 x 350 x 125 mm
Revolving screw feet:	yes
Weighing surface (WxD):	295 x 225 mm