

# KERN DS5K0.05S

Industriewaage mit Laborgenauigkeit, auch mit Eichzulassung [M]



## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

## Power supply

Charging time:	10 h
Input voltage:	100 V - 240 V
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

## Service

DAkkS Certificate:	963-127
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Platform scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	460 x 370 x 320 mm
Gross weight:	5 kg
Net weight:	4,100 kg
Shipping method:	Parcel service

## Construction

Cable length of display device:	2 m
Dimensions housing (WxDxH):	225 x 115 x 60 mm
Dimensions of display device (WxDxH):	225 x 115 x 60 mm
Dimensions of weighing plate (WxDxH):	228 x 228 x 95 mm
of stand:	45 cm
Material weighing plate:	stainless steel
Weighing surface (WxD):	228 x 228 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	150 mg
Readout [d]:	50 mg
Recommended adjusting weight:	5 kg (F1)
Reproducibility:	50 mg
Resolution:	100000
Stabilisation time:	3 s
Warm up time:	2 h
Weighing range [Max]:	5 kg
Weighing system:	Strain gauge
Weighing units:	* ct dwt g gn kg lb mo oz t tl (Cn) tl (HK) tl (Singap. Malays) tl (Tw) to

## Display

Display digit height:	1,800 cm
-----------------------	----------

## Counting

Counting resolution:	100000
Minimum piece weight at piece counting (Laboratory):	50 mg
Minimum piece weight at piece counting (Normal):	500 mg

## Functions

Counting function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Vibration-free weighing (Animal weighing program):	yes