

KERN EMB 200-2

KERN

Entry level laboratory balance with tremendous weighing performance



Category

Brand	KERN
Product category	Laboratory balance
Product group	School balance
Product family	EMB

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	200 g
Readability [d]	0,01 g
Reproducibility	0,01 g
Linearity	± 0,02 g
Resolution	20.000
Tare range	200 g

Adjustment options	Adjusting with external weight
Recommended adjusting weight	200 g (M1)
Possible calibration points	200 g
Stabilization time	2,5 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,03 g
Construction type of the scale	Single-range balance

Units	g
	dwt
	ozt
	oz
Maximum creep (15 minutes)	40 mg
Maximum creep (30 minutes)	80 mg
Default unit	g

Display

Display type	LCD
--------------	-----

Display backlight	no
Display screen size	58×18 mm
Display digit height	15 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	170×244×39 mm
Dimensions weighing surface (Ø)	105 mm
Dimensions weighing surface	105 mm
Material housing	plastic
Material weighing plate	plastic
Material display housing	plastic

Functions

Underfloor weighing	Hook (included in delivery)
IP protection - complete device	-
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Tare function	manual (multi)
Number of keys for operation	2

Power Supply

Supplied power supply	Battery
Power supply type	Power adapter
Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
Input voltage device / power [Max]	CH
	9 V, 300 mA
Power socket for mains adapter	Hollow plug, inside minus, Ø inside 2,1 mm, Ø outside 5,5 mm, long 12 mm
Battery / accumulator type	Alkali(-Manganese)
Battery	9 V block
Battery connection	Pad + Spring
Battery operating time	25 h
Battery voltage	9 V
Battery - Number of cells	1
Battery - Individual weight	45,5 g
Battery - Total weight	45,5 g
Rechargeable battery	KS-A01
Rechargeable battery operating time - backlight off	50 h
Rechargeable battery charging time	10 h
Rechargeable battery optional	Rchrg. battery optional
Battery/Accu connected	not connected, enclosed

KERN EMB 200-2



Entry level laboratory balance with tremendous weighing performance

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-247
Article number for DAkkS calibration	963-127
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	210×267×89 mm
Shipping method	Parcel service
Net weight approx.	0,50 kg
Gross weight approx.	0,70 kg
Shipping weight	1 kg

Product information

GTIN/EAN number	4045761068469
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

