

KERN EMB 200-3V

Kompakt-Laborwaage mit integrierter Dichtebestimmungsfunktion



Power supply

Charging time:	10 h
Input voltage:	230 V AC 50 Hz
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time:	12 h
Operating time (Backlight off):	50 h
Rechargeable battery:	Rchrg. battery optional

Service

DAkkS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	220 x 290 x 150 mm
Gross weight:	1,415 kg
Net weight:	835 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	175 x 245 x 54 mm
Material weighing plate:	Plastic
Weighing surface (d):	82

Measuring system

Adjustment options:	External calibration
Linearity:	5 mg
Readout [d]:	1 mg
Recommended adjusting weight:	200 g (F1)
Reproducibility:	2 mg
Resolution:	200000
Stabilisation time:	2,500 s
Warm up time:	2 h
Weighing range [Max]:	200 g
Weighing system:	Strain gauge
Weighing units:	ct g

Display

Display digit height:	1,500 cm
-----------------------	----------

Functions

Density determination function:	yes
Suspended weighing:	Hook

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C
Minimum humidity:	5 %