

# KERN EMB 6000-1

Einsteiger-Laborwaage mit enormen Wägeleistungen



n/a: Mains adapter external

## Power supply

Operating time: 12 h  
Operating time (Backlight off): 50 h  
Rechargeable battery: Rchrg. battery optional

## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

## Category

Brand: KERN  
Category: Balances  
Product Group: School balance

## Packaging & shipping

Delivery: 24 h  
Dimensions packaging (WxDxH): 200 x 265 x 66 mm  
Gross weight: 718 g  
Net weight: 548 g  
Shipping method: Parcel service

## Construction

Casing material: Plastic  
Dimensions housing (WxDxH): 170 x 240 x 39 mm  
Material weighing plate: Plastic  
Weighing surface (d): 150

## Measuring system

Adjustment options: External calibration  
Linearity: 300 mg  
Readout [d]: 100 mg  
Recommended adjusting weight: 5 kg (M1)  
Reproducibility: 100 mg  
Resolution: 60000  
Stabilisation time: 3 s  
Warm up time: 2 h  
Weighing range [Max]: 6 kg  
Weighing system: Strain gauge  
Weighing units: dwt g oz ozt

## Display

Display digit height: 1,500 cm

## Functions

Suspended weighing: Hook

## Environmental conditions

Maximum humidity: 80 %  
Maximum operating temperature: 35 °C  
Minimum ambient temperature: 5 °C

## Power supply

Charging time: 10 h