


KERN EMS 300-3

KERN

Entry level model in the low-cost range with large weighing plate



Category

Brand	KERN
Product category	Laboratory balance
Product group	School balance
Product family	EMS

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	300 g
Readability [d]	0,001 g
Reproducibility	0,002 g
Linearity	± 0,005 g
Resolution	300.000
Tare range	300 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	300 g (F1)
Possible calibration points	300 g
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,005 g
Construction type of the scale	Single-range balance
Units	g dwt ozt oz
Maximum creep (15 minutes)	10 mg
Maximum creep (30 minutes)	20 mg
Default unit	g

Display

Display type	LCD
--------------	-----

Display backlight	no
Display digit height	25 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	200×280×65 mm
Dimensions completely mounted (W×D×H)	200×280×126 mm
Dimensions rectangular draught shield - inner (W×D×H)	145×145×65 mm
Dimensions rectangular draught shield - outer (W×D×H)	165×165×80 mm
Dimensions weighing surface (Ø)	105 mm
Dimensions weighing surface	105 mm
Material housing	plastic
Material weighing plate	plastic, with conductive lacquer
Material display housing	plastic

Functions

Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Counting function	✓
Counting resolution (laboratory conditions)	150.000
Smallest piece weight when piece counting - laboratory conditions	2 mg
Smallest piece weight when piece counting - normal conditions	20 mg
Reference quantity	5, 10, 20, 25, 50
IP protection - complete device	-
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Tare function	manual (multi)
Number of keys for operation	5

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	9 V, 300 mA
Power socket for mains adapter	Hollow plug, inside minus, Ø inside 2,1 mm,

KERN EMS 300-3

KERN

Entry level model in the low-cost range with large weighing plate

Ø outside 5,5 mm, long
12 mm

Battery / accumulator type	Alkali(-Manganese)
Battery	9 V block
Battery connection	9V Bloc
Battery operating time	40 h
Rechargeable battery operating time - backlight off	50 h
Rechargeable battery optional	Rchrg. battery optional

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Min]	40 %
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-127
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	240×485×170 mm
Shipping method	Parcel service
Net weight approx.	1,4 kg
Gross weight approx.	2,2 kg
Shipping weight	4 kg

Product information

GTIN/EAN number	4045761133129
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

