



Discover more details and matching accessories online!

Heavy duty parcel and veterinary platform scale with extra large stainless steel weighing plate

Features	Technical data
• Weighing plate stainless steel, painted steel base • Simple and convenient 4-key operation • Wall mount for display device, standard • Hold function: When the weighing conditions are unstable, a stable weight is calculated determining an average value • 1 The scale can be easily transported using rollers and a handle and does not require much storage space • Protective working cover included with delivery • Non-slip rubber mat included with delivery • Universal external mains adapter included with delivery	• Large LCD display, digit height 25 mm • Weighing platform dimensions, stainless steel, W×D×H 950×500×58 mm • Dimensions of display device W×D×H 235×114×51 mm • Cable length display device, spiral cable, approx. 2,7 m • Optional battery operation, 4×1.5 V AA not included in scope of delivery, operating time up to 60 h • Permissible ambient temperature 5 °C/35 °C

STANDARD



OPTION



Model	Weighing capacity	Readability	Reproducibility	Linearity	Net weight	Options
						Calibr. Certificate
	[Max]	[d]			approx.	DAkkS accr.
KERN	kg	g	g	g	kg	KERN
EOS 150K50XL	150	50	50	± 100	19	963-129
EOS 300K100XL	300	100	100	± 200	19	963-129