## KERN FCB8K0.1



Bench scale with second display on the backside of the scale



Measuring system	
Adjustment options:	External calibration
Linearity:	300 mg
Readout [d]:	100 mg
Recommended adjusting weight:	5 kg (F2); 2 kg (F2); 1 kg (F2)
Reproducibility:	100 mg
Resolution:	80000
Stabilisation time:	3 s
Tare range:	8 kg
Warm up time:	2 h
Weighing range [Max]:	8 kg
Weighing system:	Strain gauge
Weighing units:	dwt g lb mo oz ozt tl (HK) tl (Tw) tol
Display	

2,500 cm
40000
200 mg
2 g

## Functions

Counting function:		yes	
Percentage determinat	ion:	yes	
Vibration-free weighing weighing program):	(Animal	yes	
Percentage determinat Vibration-free weighing		,	

Environmental conditions	
Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C
Power supply	
Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US
n/a:	Mains adapter external
Power supply	
Operating time:	12 h
Operating time (Backlight off):	10 h
Operating time (Backlight on):	5 h
Rechargeable battery:	Rchrg. battery optional
Service	
DAkkS Certificate:	963-128
Category	
Brand:	KERN
Category:	Balances
Product Group:	Bench scale
Packaging & shipping	
Delivery:	24 h
Dimensions packaging (WxDxH):	335 x 400 x 190 mm
Gross weight:	3,393 kg
Net weight:	2,715 kg
Shipping method:	Parcel service
Construction	
Casing material:	Plastic
Dimensions housing (WxDxH):	270 x 345 x 106 mm
Dimensions of weighing plate (WxDxH):	252 x 228 x 12,5 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	252 x 228 mm