

KERN FL500

Premium-Kraftmessinstrument mit grafikunterstütztem Display



Measuring system

Measuring range [Max]:	500 N
Overload protection (of [Max]):	120 %
Precision (of [Max]):	0,002
Readout [d]:	0,200 N
Test frequency:	1000 Hz

Display

Display digit height:	8,500 mm
-----------------------	----------

Functions

Data hold function:	yes
Function to set limits:	yes
Peak function:	yes

Environmental conditions

Maximum operating temperature:	35 °C
Minimum ambient temperature:	15 °C

Power supply

Charging time:	8 h
Input voltage:	100 V - 240 V
n/a:	CH EURO

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	10 h
---------------------------------	------

Service

DAkkS Calibration certificate (Pressure):	963-261
---	---------

DAkkS Calibration certificate (Tensile):	963-161
--	---------

DAkkS Calibration certificate (Tensile/Pressure):	963-361
---	---------

DAkkS Certificate:	963-161
--------------------	---------

ISO calibration certificate:	961-361
------------------------------	---------

ISO Calibration certificate (Pressure):	961-261
---	---------

ISO Calibration certificate (Tensile):	961-161
--	---------

ISO Calibration certificate (Tensile/Pressure):	961-361
---	---------

Category

Brand:	Sauter
Category:	Force gauges
Product Group:	Electronic force-measuring device

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	345 x 295 x 87 mm
Gross weight:	1,386 kg
Net weight:	515 g
Shipping method:	Parcel service
UN number:	3496

Construction

Casing material:	Metal lacquered
Dimensions of display device (WxDxH):	175 x 75 x 30 mm
Overall dimensions mounted (WxDxH):	175 x 75 x 30 mm