

KERN FOB 500-1S

Preiswerte Edelstahlwaage in kompakter Bauform



Service

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127

Category

Brand: KERN

Category: Balances

Product Group: Bench scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 220 x 190 x 75 mm

Gross weight: 839 g

Net weight: 675 g

Shipping method: Parcel service

Construction

Casing material: stainless steel

Dimensions housing (WxDxH): 175 x 155 x 40 mm

Material weighing plate: stainless steel

Weighing surface (WxD): 125 x 155 mm

Measuring system

Adjustment options: External calibration

Linearity: 200 mg

Readout [d]: 100 mg

Recommended adjusting weight: 500 g (M1)

Reproducibility: 100 mg

Resolution: 5000

Stabilisation time: 2 s

Tare range: 500 g

Warm up time: 10 min

Weighing range [Max]: 500 g

Weighing system: Strain gauge

Weighing units: dwt g lb oz ozt

Display

Display digit height: 2 cm

Environmental conditions

Maximum humidity: 95 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: 10 °C

Minimum humidity: 25 %

Power supply

Input voltage: 230 V AC 50 Hz

n/a: Mains adapter external

Power supply

Operating time: 20 h