

KERN FOB5K1S

Preiswerte Edelstahlwaage in kompakter Bauform



Service

Adjustment at the location of installation: 961-247

DAkKS Certificate: 963-127

Category

Brand: KERN

Category: Balances

Product Group: Bench scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 190 x 212 x 75 mm

Gross weight: 843,300 g

Net weight: 678,200 g

Shipping method: Parcel service

Construction

Casing material: stainless steel

Dimensions housing (WxDxH): 175 x 150 x 40 mm

Material weighing plate: stainless steel

Weighing surface (WxD): 125 x 155 mm

Measuring system

Adjustment options: External calibration

Linearity: 2 g

Readout [d]: 1 g

Recommended adjusting weight: 5 kg (M1)

Reproducibility: 1 g

Resolution: 5000

Stabilisation time: 2 s

Tare range: 5 kg

Warm up time: 10 min

Weighing range [Max]: 5 kg

Weighing system: Strain gauge

Weighing units: dwt g lb oz ozt

Display

Display digit height: 2 cm

Environmental conditions

Maximum humidity: 95 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: 10 °C

Minimum humidity: 25 %

Power supply

Input voltage: 230 V AC 50 Hz

n/a: Mains adapter external

Power supply

Operating time: 20 h