

KERN HCB20K10

Die Handlichen für erhöhte Lasten bis 1 Tonne!

KERN[®]



Measuring system

Adjustment options:	External calibration
Linearity:	20 g
Precision (of [Max]):	0,005
Readout [d]:	10 g
Recommended adjusting weight:	10 kg (M3)
Reproducibility:	10 g
Resolution:	2000
Stabilisation time:	2 s
Warm up time:	10 min
Weighing range [Max]:	20 kg
Weighing system:	Strain gauge
Weighing units:	kg lb N

Display

Display digit height:	1,200 cm
-----------------------	----------

Functions

Data hold function:	yes
---------------------	-----

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Operating time:	300 h
-----------------	-------

Service

Adjustment at the location of installation: 961-248

DAkkS Certificate:	963-128H
--------------------	----------

Category

Brand:	KERN
Category:	Balances
Product Group:	Hanging scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	215 x 152 x 85 mm
Gross weight:	870 g
Net weight:	570 g
Shipping method:	Parcel service
UN number:	2800

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	80 x 45 x 150 mm