

# KERN HK-D.

Premium-Durometer für Härteprüfungen



## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	368 x 220 x 87 mm
Gross weight:	1,540 kg
Net weight:	450 g
Shipping method:	Parcel service

## Construction

Casing material:	Cast aluminium alloys
Overall dimensions mounted (WxDxH):	132 x 82 x 31 mm

## Measuring system

Measuring range (Max):	960
Measuring range (Min):	170
Precision (of [Max]):	1 %
Readout:	1
Sensor:	D
Weighing units:	HB HL HRB HRC HV

## Display

Display digit height:	1,100 cm
-----------------------	----------

## Functions

All measurement directions possible (360°):	yes
Automatic recognition of the impact sensor:	yes
Obtaining average:	yes

## Environmental conditions

Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

## Power supply

Operating time:	200 h
-----------------	-------

## Service

ISO calibration certificate:	961-131
------------------------------	---------

## Category

Brand:	Sauter
Category:	Hardness testers
Product Group:	Electronic Leeb hardness tester