

KERN IFS60K0.5DL

Industriezählwaage mit komfortabler Zehnertastatur zur bequemen Dateneingabe, Zählauflösung 75000 Punkte



Measuring system

Adjustment options:	External calibration
Linearity:	3 g 6 g
Readout [d]:	500 mg 1000 mg
Recommended adjusting weight:	50 kg (F2)
Reproducibility:	500 mg 1000 mg
Resolution:	60 60.000
Stabilisation time:	3 s
Tare range:	-60000000 mg
Warm up time:	2 h 2 h
Weighing range [Max]:	30 kg 60 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height:	1,650 cm
Display digit height:	1,300 cm

Counting

Counting resolution:	60000
Minimum piece weight at piece counting (Laboratory):	1 g
Minimum piece weight at piece counting (Normal):	10 g

Functions

Counting function:	yes
Function to save totals:	yes
Peak function:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	40 h
Operating time (Backlight on):	30 h
Rechargeable battery:	Rchrg. battery optional (factory)

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	555 x 935 x 220 mm
Gross weight:	14,600 kg
Net weight:	12 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	3 m
Dimensions of display device (WxDxH):	260 x 150 x 65 mm
Dimensions of weighing plate (WxDxH):	400 x 500 x 120 mm
of stand:	60 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	500 x 400 mm