KERN **MBC-A01**

Mechanical height rod to fix to the scale, measuring range 10 cm – 80 cm, increments of 1 mm



Category

Brand	KERN
Product categoriy	Balance
Product group	Height rod

Measuring System

Measuring range measuring rod (cm)	10-80cm @ 0,1cm ± 0,5cm
Measuring range length [Min]	10 cm
Linearity	±
Units	inch inch/ft cm
Measuring range length [Max]	80 cm
Tolerance measuring rod	5 mm
Division	1 mm

Construction

Dimension housing (W×D×H)	900×300×180 mm
Dimensions device (W×D×H)	900×465×180 mm
Material housing	plastic
Measurement alignment	horizontal

Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Humity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
Approval in accordance with 2017/745 (MDR, med.)	✓

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	180×890×140 mm
Shipping method	Parcel service
Net weight approx.	0,80 kg
Gross weight approx.	1,4 kg
Shipping weight	4,5 kg

Product information

GTIN/EAN number	4045761133624
REACH classification	no prohibited substances

Pictograms

STANDARD



CE
0297