

KERN MPC250K100M



Professionelle Personenwaage mit Eich- und Medizinzulassung für den professionellen Einsatz in der medizinischen Diagnostik



Functions

| | |
|----------------------------------------------------|-----|
| BMI function: | yes |
| Data hold function: | yes |
| PRE-TARE function: | yes |
| Vibration-free weighing (Animal weighing program): | yes |

Environmental conditions

| | |
|--------------------------------|--------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 40 °C |
| Minimum ambient temperature: | -10 °C |

Power supply

| | |
|----------------|--------------------------|
| Charging time: | 12 h |
| Input voltage: | 100 V - 240 V 50 / 60 Hz |
| n/a: | CH EURO UK |

n/a: Mains adapter external

Power supply

| | |
|---------------------------------|----------------------------------|
| Operating time: | 20 h |
| Operating time (Backlight off): | 40 h |
| Operating time (Backlight on): | 20 h |
| Rechargeable battery: | Rchrg. battery optional - intern |

Service

Adjustment at the location of installation: 961-249

| | |
|--------------------|---------|
| DAkkS Certificate: | 963-129 |
| Verification: | 965-129 |

Category

| | |
|----------------|----------------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Personal floor scale |

Packaging & shipping

| | |
|-------------------------------|--------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 560 x 440 x 200 mm |
| Gross weight: | 10,020 kg |
| Net weight: | 8,400 kg |
| Shipping method: | Parcel service |

Construction

| | |
|---------------------------------------|-------------------|
| Cable length of display device: | 1,800 m |
| Casing material: | Steel lacquered |
| Dimensions of display device (WxDxH): | 200 x 130 x 60 mm |

Measuring system

| | |
|-------------------------------|----------------------|
| Adjustment options: | External calibration |
| Linearity: | 100 g |
| Readout [d]: | 100 g |
| Recommended adjusting weight: | 200 kg (M1) |
| Reproducibility: | 100 g |
| Resolution: | 2500 |
| Stabilisation time: | 3 s |
| Tare range: | 249,900 kg |
| Warm up time: | 10 min |
| Weighing range [Max]: | 250 kg |
| Weighing system: | Strain gauge |
| Weighing units: | kg |

Display

| | |
|-----------------------|----------|
| Display digit height: | 2,500 cm |
|-----------------------|----------|

Technical data about verification

| | |
|-------------------------------------------------|---------|
| Minimum load [Min]: | 2 kg |
| Periodic Verification for Italy: | 969-112 |
| Verification approval conforming to 2014/31/EU: | yes |
| Verification by KERN possible: | yes |
| Verification class: | III |
| Verification value [e]: | 100 g |

KERN MPC250K100M



Professionelle Personenwaage mit Eich- und Medizinzulassung für den professionellen Einsatz in der medizinischen Diagnostik

| | |
|---------------------------------------|-------------------|
| Dimensions of weighing plate (WxDxH): | 365 x 370 x 80 mm |
| Level indicator: | yes |
| Material weighing plate: | Plastic |
| Wall mount: | yes |