

KERN MTS300K100M

Preisgünstige Stehhilfewaage für ein sicheres Gefühl beim Wiegen - mit Eich- und Medizinzulassung



Verification by KERN possible: yes

Verification class: III

Verification value [e]: 100 g

Functions

BMI function: yes

Data hold function: yes

PRE-TARE function: yes

Vibration-free weighing (Animal weighing program): yes

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 35 °C

Minimum ambient temperature: 5 °C

Power supply

Input voltage: 100 V - 240 V 50 / 60 Hz

n/a: CH EURO UK

n/a: Mains adapter external

Power supply

Operating time: 50 h

Operating time (Backlight on): 45 h

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Verification: 965-129

Category

Brand: KERN

Category: Balances

Product Group: Handrail scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 1050 x 670 x 170 mm

Gross weight: 26,300 kg

Net weight: 21,800 kg

Shipping method: Parcel service

Construction

Casing material: Steel lacquered

Dimensions of display device (WxDxH): 210 x 110 x 50 mm

Measuring system

Adjustment options: External calibration

Linearity: 100 g

Readout [d]: 100 g

Recommended adjusting weight: 250 kg (M1)

Reproducibility: 100 g

Resolution: 3000

Warm up time: 10 min

Weighing range [Max]: 300 kg

Weighing system: Strain gauge

Weighing units: kg

Display

Display digit height: 2,500 cm

Technical data about verification

Minimum load [Min]: 2 kg

Periodic Verification for Italy: 969-112

Verification approval conforming to 2014/31/EU: yes

KERN MTS300K100M



Preisgünstige Stehhilfewaage für ein sicheres Gefühl beim Wiegen - mit Eich- und Medizinzulassung

Dimensions of weighing plate (WxDxH):	550 x 550 x 62 mm
of stand:	1 m
Level indicator:	yes
Material weighing plate:	Steel lacquered
Overall dimensions mounted (WxDxH):	550 x 550 x 1060 mm
Revolving screw feet:	yes