

KERN PBS4200-2M

Multifunktions-Laborwaage mit Single-Cell-Wägesystem und Eichzulassung [M]



Functions

Counting function:	yes
Density determination function:	yes
Dispensing function:	yes
Peak function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Standby function:	yes
Suspended weighing:	Hook
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C

Power supply

Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Service

DAkkS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	450 x 370 x 255 mm
Gross weight:	4,892 kg
Net weight:	3,180 kg
Shipping method:	Parcel service

Construction

Casing material:	Cast aluminium alloys
Dimensions housing (WxDxH):	200 x 320 x 85 mm
Dimensions of weighing plate (WxDxH):	170 x 180 x 5 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	180 x 190 mm

Measuring system

Adjustment options:	External calibration
Linearity:	20 mg
n/a:	20 g
Readout [d]:	10 mg
Recommended adjusting weight:	4 kg (E2)
Reproducibility:	10 mg
Resolution:	420000
Stabilisation time:	2,500 s
Warm up time:	4 h
Weighing range [Max]:	4,200 kg
Weighing units:	g kg

Display

Display digit height:	1,400 cm
-----------------------	----------

Technical data about verification

Verification approval conforming to 2014/31/EU:	yes
Verification class:	II

Counting

Counting resolution:	420000
Minimum piece weight at piece counting (Laboratory):	10 mg
Minimum piece weight at piece counting (Normal):	100 mg