

# KERN PEJ620-3M



Robuste Labor- und Industrie-Präzisionswaage für schweres Wägegut, mit Eichzulassung [M]



## Functions

Counting function:	yes
Function to save totals:	yes
Percentage determination:	yes
Standby function:	yes
Suspended weighing:	Loop
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C

## Power supply

Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO

n/a: Mains adapter external

## Service

DAkkS Certificate:	963-127
Verification:	965-201

## Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	330 x 440 x 225 mm
Gross weight:	6,200 kg
Net weight:	4,300 kg
Shipping method:	Parcel service

## Construction

Casing material:	Cast aluminium alloys
Dimensions draft shield (WxDxH):	175 x 155 x 105 mm
Dimensions housing (WxDxH):	220 x 333 x 93 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	170 x 150 x 100 mm
Weighing surface (WxD):	140 x 120 mm

## Measuring system

Adjustment options:	Internal calibration (auto)
Linearity:	3 mg
n/a:	2 g
Readout [d]:	1 mg
Reproducibility:	1 mg
Resolution:	620000
Stabilisation time:	3 s
Warm up time:	4 h
Weighing range [Max]:	620 g
Weighing units:	ct g kg

## Display

Display digit height:	1,300 cm
-----------------------	----------

## Technical data about verification

Minimum load [Min]:	100 mg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	I
Verification value [e]:	10 mg

## Counting

Counting resolution:	620000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg