



Robust laboratory and industrial precision scale for heavy items, verification optional

- KERN PEJ: Automatic internal adjustment, guarantees high degree of accuracy and makes the balance independent of its location of use
- KERN PES: Adjusting program CAL for quick setting of the balance accuracy, external test weights at an additional price, see *test weights*
- Metal housing: robust and sturdy
- Weighing with tolerance range: a visual and audible signal helps with portioning, dispensing or grading
- Draught shield standard for models with weighing plate size **A**, weighing space W×D×H 170×150×100 mm
- **A**, **B** Underfloor weighing: Possibility of load support with built-in loop on the underside of the balance
- **A**, **B** Protective working cover included with delivery

- Fluorescent display, bright with high contrast, digit height 14 mm
- Dimensions weighing surface, stainless steel
 - A** W×D 140×120 mm
 - B** W×D 200×200 mm, see larger picture
 - C** W×D 250×220 mm
- Overall dimensions (without draught shield)
 - W×D×H
 - A, B** 220×333×93 mm
 - C** 260×330×113 mm
- Permissible ambient temperature 10 °C/30 °C



Precision Balances