

KERN PFB 2000-2



Schnellanzeigende Präzisionswaage mit komfortabler Bedienphilosophie und Eichzulassung [M]



Environmental conditions

| | |
|--------------------------------|-------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 30 °C |
| Minimum ambient temperature: | 15 °C |

Power supply

| | |
|----------------|---------------|
| Input voltage: | 110 V - 240 V |
| n/a: | CH EURO UK US |

| | |
|------|------------------------|
| n/a: | Mains adapter external |
|------|------------------------|

Service

| | |
|--------------------|---------|
| DAkkS Certificate: | 963-127 |
|--------------------|---------|

Category

| | |
|----------------|-------------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Precision balance |

Packaging & shipping

| | |
|-------------------------------|--------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 260 x 330 x 260 mm |
| Gross weight: | 2,380 kg |
| Net weight: | 1,510 kg |
| Shipping method: | Parcel service |

Construction

| | |
|-------------------------------------|--------------------|
| Casing material: | Plastic |
| Dimensions draft shield (WxDxH): | 167 x 154 x 80 mm |
| Dimensions housing (WxDxH): | 200 x 257 x 87 mm |
| Level indicator: | yes |
| Material weighing plate: | stainless steel |
| Overall dimensions mounted (WxDxH): | 200 x 257 x 152 mm |
| Revolving screw feet: | yes |
| Weighing space (WxDxH): | 158 x 143 x 64 mm |
| Weighing surface (d): | 120 |

Measuring system

| | |
|-------------------------------|--------------------------------------------------------------|
| Adjustment options: | External calibration |
| Linearity: | 30 mg |
| n/a: | 40 g |
| Readout [d]: | 10 mg |
| Recommended adjusting weight: | 2 kg (F1) |
| Reproducibility: | 20 mg |
| Resolution: | 200000 |
| Stabilisation time: | 3 s |
| Warm up time: | 2 h |
| Weighing range [Max]: | 2 kg |
| Weighing system: | Strain gauge |
| Weighing units: | bat ct dot dwt g lb mo N oz ozt t tl (Cn) tl (HK) tl (Tw) |

Display

| | |
|-----------------------|----------|
| Display digit height: | 1,650 cm |
|-----------------------|----------|

Counting

| | |
|------------------------------------------------------|--------|
| Counting resolution: | 100000 |
| Minimum piece weight at piece counting (Laboratory): | 20 mg |
| Minimum piece weight at piece counting (Normal): | 200 mg |

Functions

| | |
|---------------------------|-----|
| Counting function: | yes |
| Percentage determination: | yes |