

KERN PFB6K0.05



Schnellanzeigende Präzisionswaage mit komfortabler Bedienphilosophie und Eichzulassung [M]



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	15 °C

Power supply

n/a:	CH EURO UK US
------	---------------

n/a:	Mains adapter external
------	------------------------

Service

DAkkS Certificate:	963-128
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	255 x 330 x 255 mm
Gross weight:	2,280 kg
Net weight:	1,520 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	200 x 255 x 87 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	200 x 255 x 87 mm
Revolving screw feet:	yes
Weighing surface (WxD):	155 x 145 mm

Measuring system

Adjustment options:	External calibration
Linearity:	150 mg
n/a:	100 g
Readout [d]:	50 mg
Recommended adjusting weight:	5 kg (F1)
Reproducibility:	50 mg
Resolution:	120000
Stabilisation time:	3 s
Warm up time:	2 h
Weighing range [Max]:	6 kg
Weighing system:	Strain gauge
Weighing units:	bat ct dot dwt g lb mo N oz ozt t tl (Cn) tl (HK) tl (Tw)

Display

Display digit height:	1,650 cm
-----------------------	----------

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	200 mg
Minimum piece weight at piece counting (Normal):	2 g

Functions

Counting function:	yes
Percentage determination:	yes