

KERN PLJ720-3A



Präzisionswaagenserie mit enormen Wägebereichen â ideal bei schweren Taragefäßen oder großen Proben



Measuring system

Adjustment options:	Internal calibration (auto)
Linearity:	2 mg
n/a:	2 g
Readout [d]:	1 mg
Reproducibility:	1 mg
Resolution:	720000
Stabilisation time:	2 s
Tare range:	720 g
Warm up time:	4 h
Weighing range [Max]:	720 g
Weighing system:	Force compensation
Weighing units:	ct dwt g gn lb mo oz ozt tl (HK) tl (Singap. Malays) tl (Tw)

Display

Display digit height:	1,700 cm
-----------------------	----------

Counting

Counting resolution:	720000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg
Reference weight:	yes

Functions

Counting function:	yes
Density determination function:	yes
Peak function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Standby function:	yes
Suspended weighing:	Loop
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Service

DAkkS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	500 x 360 x 420 mm
Gross weight:	7,320 kg
Net weight:	4,900 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions draft shield (ÃxH):	160 70
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	210 x 340 x 160 mm
Revolving screw feet:	yes
Weighing space (ÃxH):	150 60
Weighing surface (d):	80