



Discover more details and matching accessories online!

Retail scale with memories for item prices

Features

- 1 KERN RPB-HM: Elevated display backlit, revolving on column, height of stand approx. 480 mm
- 2 KERN RPB-M: Second display on the back of the balance
- Three displays for weight display (verifiable), unit price, total price
- Memory (PLU) for 10 article prices
- Unit price can be switched from €/kg to €/100 g
- Auto-clear-key: Unit price entry is automatically set to zero when scale is unloaded
- 3 Thanks to rechargeable battery operation (optional), compact, lightweight construction, it is suitable for the use in several locations
- Protective working cover included with delivery

Technical data

- Large backlit LCD displays, digit height 15 mm
- Dimensions weighing surface, stainless steel, WxD 204x263 mm
- Overall dimensions WxDxH
KERN RPB-M: 283x318x110,3 mm
KERN RPB-HM: 283x375,5x486,8 mm
- Net weight
KERN RPB-M: approx. 2,8 kg
KERN RPB-HM: approx. 3,2 kg
- Permissible ambient temperature -10 °C/40 °C

Main scope of applications

- Retail shops
- Weekly markets
- Farm shops
- Fruit and vegetable sales

Note: Official verification is mandatory for commercial trade

STANDARD

OPTION

Model	Weighing capacity	Readability	Verification value	Minimal load	Options	
					Verification	Calibr. Certificate
KERN	[Max] kg	[d] g	[e] g	[Min] g	 KERN	DAkkS accr. KERN
	Multi-division balance, with increasing or decreasing load, it switches automatically to the next largest or smallest weighing range [Max] and readout [d].					
RPB 3K3DM	1,5 3	0,5 1	0,5 1	10	965-227	963-127
RPB 6K1DM	3 6	1 2	1 2	20	965-228	963-128
RPB 15K2DM	6 15	2 5	2 5	40	965-228	963-128
RPB 30K5DM	15 30	5 10	5 10	100	965-228	963-128
1 with elevated display						
RPB 3K3DHM	1,5 3	0,5 1	0,5 1	10	965-227	963-127
RPB 6K1DHM	3 6	1 2	1 2	20	965-228	963-128
RPB 15K2DHM	6 15	2 5	2 5	40	965-228	963-128
RPB 30K5DHM	15 30	5 10	5 10	100	965-228	963-128

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.