

# KERN RPB6K1DM

Ladenwaage mit Eichzulassung [M] und Speicherplätzen für Artikelpreise



## Measuring system

Adjustment options:	External calibration
Linearity:	1 g   2 g
Readout [d]:	1 g   2 g
Recommended adjusting weight:	5 kg (F2); 1 kg (F2)
Reproducibility:	1 g   2 g
Resolution:	3 3.000
Stabilisation time:	2 s
Tare range:	5,998 kg
Warm up time:	10 min   10 min
Weighing range [Max]:	3 kg   6 kg
Weighing system:	Strain gauge
Weighing units:	g kg

## Display

Additional Display possible:	yes
Display digit height:	2 cm

## Technical data about verification

Minimum load [Min]:	20 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	1 g   2 g

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

## Power supply

Charging time:	14 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	80 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional - intern

## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate:	963-128
Verification:	965-228

## Category

Brand:	KERN
Category:	Balances
Product Group:	Price computing scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	370 x 450 x 215 mm
Gross weight:	4,058 kg
Net weight:	3,500 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	315 x 350 x 100 mm
Dimensions of display device (WxDxH):	315 x 350 x 125 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	320 x 350 x 125 mm
Revolving screw feet:	yes
Weighing surface (WxD):	295 x 225 mm