

KERN SFB 60K20LHIPM

Edelstahl-Plattformwaage mit Staub- und Spritzwasserschutz IP65 und Eichzulassung [M]



Technical data about verification

Minimum load [Min]:	400 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	20 g

Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	110 V - 230 V AC
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	35 h
Operating time (Backlight on):	20 h

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
Verification:	965-229

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Measuring system

Adjustment options:	External calibration
Linearity:	20 g
Readout [d]:	20 g
Recommended adjusting weight:	60 kg (M1)
Reproducibility:	20 g
Resolution:	3000
Stabilisation time:	2 s
Tare range:	-60000000 mg
Warm up time:	10 min
Weighing range [Max]:	60 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height:	5,200 cm
-----------------------	----------

KERN SFB 60K20LHIPM



Edelstahl-Plattformwaage mit Staub- und Spritzwasserschutz IP65 und Eichzulassung [M]

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	470 x 800 x 240 mm
Gross weight:	14,700 kg
Net weight:	14 kg
Shipping method:	Parcel service
UN number:	2800

Construction

Cable length of display device:	3 m
Dimensions of display device (WxDxH):	266 x 165 x 96 mm
Dimensions of weighing plate (WxDxH):	400 x 300 x 128 mm
of stand:	40 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	400 x 460 x 590 mm
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	400 x 300 mm