

KERN TB 1000-0.1F.

Ihr praktisches Arbeitsinstrument für den robusten Alltagseinsatz

KERN[®]



Construction

Cable length:	1 m
Casing material:	Plastic
Overall dimensions mounted (WxDxH):	161 x 69 x 32 mm

Measuring system

Measuring range [Max]:	100 x 1000 μm
Minimal base thickness:	300 μm
Precision (of [Max]):	3 %
Precision (Offset-Accur):	1 %
Readout [d]:	0 x 0,001 mm
Smallest sample surface, convex (radius):	1,500 mm
Smallest sample surface, flat (radius):	6 mm
Smallest sample surface,concave (radius):	2,500 cm
Weighing units:	μm inch (mil)

Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

Service

ISO calibration certificate:	961-110
------------------------------	---------

Category

Brand:	Sauter
Category:	Coating thickness
Product Group:	Coating thickness gauge

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	265 x 215 x 63 mm
Gross weight:	860 g
Net weight:	750 g
Shipping method:	Parcel service